FumeCube



What to specify	I. Single or Dual Arm	System 2. Voltage	3. Pre-filter	4. Main filter 6. Interfacing Kit	
1 2	Single	Single Arm System		Dual Arm System	
Voltage	230V ±10%	120V ±10%	230V ±10%	120V ±10%	
Vacuum Control	072066	072067	072065	072068	
Wattage	0.14 kW	0.107 kW	0.14 kW	0.107 kW	
Frequency	50Hz / 60 Hz	50Hz / 60 Hz	50Hz / 60 Hz	50Hz / 60 Hz	
Cabinet height	366 mm	366 mm	366 mm	366 mm	
Cabinet width (not inc hose)	308 mm	308 mm	308 mm	308 mm	
Cabinet depth (not inc hose)	294 mm	294 mm	294 mm	294 mm	
Cabinet weight (inc filters)	17 Kg	17 Kg	17 Kg	17 Kg	
Construction	Precision engineered brushed stainless steel units. High performance continuous run brushless motors. Quick and simple to relocate.				

3		Pre-filt	er Pad	
	Options: F5 Pack of 4 (std) F6 Pack of 4 F8/F9 Pack of 4	Code: 200225 200226 200316		
4		Main	filter	
	Options: HEPA/Chemical (std) Chemical	Code: 110536 110537	Options: Solvent Lock * Use in combination v	Code: 110543 vith 200316

	HEPA/Chemical Cleanroom* 110538	Note: FumeCubes sold prior to December 2008 may require different filters. Please contact your local distributor for advice.		
6	Machine Interfa	acing (Optional)		
Your Machine 10011010 Extractor	• Filter Blocked Warning: A signal is sent to a connected piece of			
Allows the Purex system to interface with a piece of equipment connected to it.	equipment to trigger an alert or to shut it down. • Remote ON/OFF Switch: 5M cable & switch See PAGE 34			
£				

Single arm system supplied with: I x Filter + pre-filter pad

- I x 51mm x 2m flexible hose [black]
- 2 x Connecting cuffs [black]
- I x Clamped bracket
- I x 38mm stainless steel flexible arm and valve
- I x 38mm pen nib nozzle & I x conical cowl.
- Controls

Visual and Audible Filter Blocked Warning

Alerts the operator when a filter starts to block so that a replacement filter can be acquired and downtime can be avoided.

LED Filter Status

Green = Filter OK Yellow = Filter nearly full Red = Filter full, replacement required


Interface with other equipment e.g. a laser optional.

Dual arm system supplied with:

- I x Filter + pre-filter pad

- - System Features...
 - Automatic electronic flow control maintains a constant extraction rate even as the filter blocks
 - Adjustable airflow
 - VariColour filter blocked warning system
 - Low capital and running costs
 - · Quick change pre-filters deliver longer filter life
 - Submicronic (HEPA) filtration removes 99.997% of
 - particles down to 0.3 microns
 - Activated carbon filtration removes harmful gas
 - Simple to install and quiet in operation • Easy to relocate
 - Precision made from stainless steel





7) Filter identification label.

In cleanroom filters, positions 3&4 are reversed.

Includes:

- I x Main filter
- 4 x Pre-filter pad
- I or 2 Arm Kit
- I x Power cable

Accessories

Please see the accessories section at the back of this brochure.

- 2 x 51mm x 2m flexible hose [black] 4 x Connecting cuffs [black]
- 2 x Clamped bracket 2×38 mm stainless steel flexible arm and valve
- 2×38 mm pen nib nozzle and $2 \times conical cowl.$